



# Net Select, Module, 8-Way Coax, 2.3GHz, Plastic

By Bryant  
Catalog # NSOVM82G



Net Select, Module, 8-Way Coax, 2.3GHz, Plastic

## Features

- Made of High impact plastic resistant material
- Pre-mounted push pins snap the module quickly into place

## Application

- CATV

## General

Catalog Number	NSOVM82G
Contact	Phosphor Bronze
EU RoHS Indicator	Yes
Enclosure Type	Integral
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	8-Way Coax, 2.3GHz
Material - Mounting Hardware Specifications	Screw Mounting <ul style="list-style-type: none"> <li>• Dimensions - 6.47 in. W x 2.09 in. H x 3.20 in. D</li> <li>• Material - High impact plastic</li> </ul>
Style	Coaxial Splitter
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Type	Coaxial Splitter

UPC 883778504419

## Dimensions

Display Size Standard Sized Product

## Electrical Ratings

Connectivity	Plug-In
Contact Resistance	Per TIA
Insertion Loss	Per TIA

## Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• RoHS Compliant</li> <li>• UL and cUL Listed</li> </ul>
----------------------	---

## Logistics

Carton Quantity 10

## Product Assets

- [Catalog Page - PREM S08 Catalog Page](#)
- [Catalog Page - PREM S8 CatalogPage](#)
- [Catalog Page - BRY R-5 Catalog Page](#)
- [Catalogs - Premise Wiring Catalog](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - NSOVM82G](#)