BRYANT®

Switches and Lighting Controls, Combination Devices, Residential Grade, 2) Single Pole Toggles, 15A 120V AC, Self Grounding, Side Wired, Brown

By Bryant Catalog # RC101AL

Switches and Lighting Controls, Combination Devices, Residential Grade, 2) Single Pole Toggles, 15A 12OV AC, Self Grounding, Side Wired, Brown



- · Quiet snap action mechanism
- Self-grounding staple is standard
- Elongated strap with continuous plaster ears

Application

Residential

General

Action Snap Switch
Actuator Toggle
Contact Configuration Two Position

Environmental Conditions Indoor Dry Unless Protected

By Additional Means

Item Type Traditional Switch Combo

Devices

Material - Mounting Hardware Mounting Screws
Number Of Poles 2) Single Pole
Operating Cycles 30,000 Minimum

Operating Temperature Max Continuous- 60 Degrees C, Minimum- -20 Without

Impact

UPC 883778109805

Dimensions

Display Size Standard Size



Electrical Ratings

Amperage Rating 15 A

Connectivity Side Wired

Contact Rating 15A
Current / Amperage Rating 15 A
Current Rating 15 A
Voltage Rating 120 VAC
Wattage 1800

Logistics

Carton Quantity 10

Product Assets

Related Products

RC108LATR - Combination Devices, Residential Grade, 1) Single Pole Toggle, 1) Single Tamper Resistant Receptacle, 15A 120VAC, SelfGrounding, Side Wired

RC108I - Combination Devices, Residential Grade, 1) Single Pole Toggle, 1) Single Receptacle, 15A 120V AC, Self Grounding, Side Wired

RC108ITR - Combination Devices, Residential Grade, 1) Single Pole Toggle, 1) Single Tamper Resistant Receptacle, 15A 120V AC, SelfGrounding, Side Wired

RC109I - Combination Devices, Residential Grade, 1) Single Pole Toggle, 1) Pilot Light, 15A 120V AC, Self Grounding, Side Wired

RC108W - Combination Devices, Residential Grade, 1) Single Pole Toggle, 1) Single Receptacle, 15A 120V AC, Self Grounding, Side Wired

