



# TradeSelect, Straight Blade Devices, Residential Grade, Receptacles, Decorator Duplex, 15A 125V, 2-Pole 3- Wire Grounding, 5-15R, Push Terminals

By Bryant  
Catalog # [RRD15W](#)



tradeSELECT® Straight Blade Residential Grade, Decorator Duplex, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Push Terminals

## Application

Residential Receptacles

## General

Color	<ul style="list-style-type: none"> <li>• White</li> <li>• Blanc</li> </ul>
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Decorator Duplex
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
UPC	883778100116

## Dimensions

Display Size Standard Sized Product

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Eight Push Wire Holes
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC
Wattage	1875

## Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG

## Certifications and Compliance

Nema Rating 5-15R

## Logistics

Carton Quantity 10

## Product Assets

[Catalog Page - Bryant A-18 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)

## Related Products

- [RRD201W - TradeSelect, Straight Blade Devices, Residential Grade, Receptacles, Decorator Single, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Self Grounding](#)
- [RRD15SW - TradeSelect, Straight Blade Devices, Residential Grade, Receptacles, Decorator Duplex, Self Grounding, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, White](#)
- [RRD205W - TradeSelect, Straight Blade Devices, Residential Grade, Receptacles, Decorator Single, 20A 250V, 2-Pole 3-Wire Grounding, 6-20R, White](#)
- [RRD151W - TradeSelect, Straight Blade Devices, Residential Grade, Receptacles, Decorator Single, 15A 125V, 2-Pole 3- Wire Grounding, 5-15R, White](#)
- [RRD15 - TradeSelect, Straight Blade Devices, Residential Grade, Receptacles, Decorator Duplex, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Brown](#)



A proud member of the Hubbell Family.