

IEC Pin and Sleeve

32 A, 100-130 VAC, 2-POLE, 3-WIRE

Receptacle

Features

- IP67 environmental ratings
- Impact and corrosion resistant insulated non-metallic housing
- Sequential contact engagement to prevent a momentary over-voltage
- Color coded housings provide quick identification of mating devices

Ordering Information

| Description | Series | Color | UPC Number | Catalog Number |
|---|-----------------|--------|--------------|------------------|
| Heavy Duty Products, IEC Pin and Sleeve | Watertight IP67 | Yellow | 781786782631 | BRY332R4W |

Listings

VDE, CE

Specifications

| | |
|-------------|---------------------------|
| Application | High Ampacity Connections |
| Connection | Screwless Spring |
| Wire Size | #10AWG to #8AWG |
| Material | PBT |
| Mounting | Screw Mount |

Performance

Electrical

| | |
|----------------------|--------------------|
| Dielectric Voltage | Withstand 3000V AC |
| Max. Working Voltage | 600V AC RMS |


Mechanical

| | |
|-------------------------|--|
| Impact Resistance | Per CSA C22.2 No. 182.1 / UL1682 |
| Product Identification | Identification and ratings are marked on device housing |
| Terminal Identification | Terminals identified in accordance with North American and IEC conventions |

Environmental

| | |
|---------------------|---|
| Flammability | HB |
| Ingress Protection | IP67 |
| Moisture Resistance | IEC 60309-1 |
| Temperature Rating | Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact. |

BRYANT®



Complementary Products

Complementary Products

Adapter Plate, Back Box

Online Resources

Customer Sales Drawings
eCatalog

BRYANT®