

## IEC Pin and Sleeve

60/63 A, 220-240 VAC, 2-POLE, 3-WIRE

## Connector

# BRYANT®

### Features

- IP44 environmental ratings
- Impact and corrosion resistant insulated non-metallic housing
- Sequential contact engagement to prevent a momentary over-voltage
- External strain relief
- Glandless water ingress protection




### Ordering Information

| Description  | Series | Color | UPC Number   | Catalog Number   |
|--|--------|-------|--------------|------------------|
| Heavy Duty Products, Splash Proof IEC Pin and Sleeve Devices, Female, Connector Body |        | Blue  | 781786784178 | <b>BRY360C6S</b> |

### Listings

All constructions are UL Listed & cUL Listed  
FileE14633  
UL1686 Standard for Pin & Sleeve Configurations  
VDE, CE



### Specifications

|             |                           |
|-------------|---------------------------|
| Application | High Ampacity Connections |
| Connection  | Pressure Screw Terminal   |
| Wire Size   | #6AWG to #4AWG            |
| Material    | PBT                       |
| Mounting    | Cord Mounted              |

### Online Resources

Customer Sales Drawings  
eCatalog

### Performance

| Electrical              |   |
|-------------------------|---|
| Dielectric Voltage      | Withstand 3000V AC  |
| Max. Working Voltage    | 600V AC RMS   |
| Mechanical              |   |
| Impact Resistance       | Per CSA C22.2 No. 182.1 / UL1682  |
| Product Identification  | Identification and ratings are marked on device housing                             |
| Terminal Identification | Terminals identified in accordance with North American and IEC conventions          |
| Environmental           |   |
| Flammability            | HB  |
| Ingress Protection      | IP44  |
| Moisture Resistance     | IEC 60309-1   |
| Temperature Rating      | Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact. |

# BRYANT®