

# Straight Blade Devices

## 20A, 125V, 2 Pole, 3 Wire Grounding

### USB Charger Receptacles



#### Features

- High Power 5 Amp, 5 Volt USB Output
- Two Type C USB Ports
- Tamper Resistant Commercial Grade Duplex Compatible
- USB Ports Rated 10,000 Cycles

#### Ordering Information

| Description                                                | Color | UPC Number   | Catalog Number |
|------------------------------------------------------------|-------|--------------|----------------|
| Tamper Resistant 20A/125V Duplex, 5 Amp, 5 Volts USB Ports | Ivory | 781786194366 | USBB20C5I      |

#### Listings

cULus Listed to UL498, UL1310

#### Specifications

|                 |                         |
|-----------------|-------------------------|
| Face            | RTP                     |
| Base            | RTP                     |
| LED             | Green Indicator         |
| Contacts        | Plated Steel            |
| Clamp           | Plated Steel            |
| Terminal Screws | Plated Steel            |
| Mounting Strap  | .040" Zinc Plated Steel |
| Mounting Screws | Zinc Plated Steel       |
| USB Port        | Stainless Steel         |



20A STANDARD  
GRADE DEVICE

#### Online Resources

eCatalog

#### Performance

|                         |                                                                                                             |
|-------------------------|-------------------------------------------------------------------------------------------------------------|
| <b>Electrical</b>       |                                                                                                             |
| Current Interruption    | Certified for current interrupting at full rated current                                                    |
| Dielectric Voltage      | Withstands 2,000V minimum<br>Complies with USB BC1.2 Battery Charging and 3.0 Power Delivery Specifications |
| <b>Mechanical</b>       |                                                                                                             |
| Product Identification  | Ratings are a permanent part of the device                                                                  |
| Terminal Accommodation  | #14-#10 AWG copper stranded or solid conductor only                                                         |
| Terminal Identification | Terminals identified in accordance with UL 498 and CSA                                                      |
| USB Ports               | Stainless steel rated for 10,000 plug insertions and removal                                                |
| <b>Environmental</b>    |                                                                                                             |
| Flammability            | UL 94V-2                                                                                                    |
| Operating Temperature   | Maximum continuous 75°C, minimum -40°C (w/o impact)                                                         |