



Locking Devices, Bryant Power Interrupting, Industrial, Flanged Inlet, 30A 250V DC/600V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Surface Mounted

By Bryant
Catalog # 21447

Locking Devices, Bryant Power Interrupting, Industrial, Flanged Inlet, 30A 250V DC/600V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Cast Aluminum, Surface Mounted

Features

- Molded-in male contacts are resistant to damage and provide a consistently positive connection
- Insulated non-metallic housing enhances safety and abuse resistance
- Box terminals in conjunction with screws with pressure pads provide maximum termination strength and dependability
- Metallic weather protective spring loaded cover provides protection from moisture and dust

Application

Extra Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No

Conductor

Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG
Number Of Poles	3-Pole

Current

Amperage Rating	20A/30 A
Voltage Rating Description	250 VDC/600 VAC
Dielectric Strength	Withstands 3000V Minimum in
Current/Amperage Rating Description	20 Amp /30 Amp
Current Rating	20A/30 A



Voltage Rating	250 VDC/600 VAC
Connectivity	Pressure Terminal Screws

Dimensions

Length	3.28 in
Display Size	Standard Sized Product
Height	1.75 in
Width	1.94 in
Dimensions	3.28 in x 1.94 in x 1.75 in

General

Color	Aluminum
Style	Grounding
UPC	781786618671
Type	Flanged Inlet
Material - Mounting Hardware	Screw Mounting
Insulation	Insulated Body
Item Type	20A/30A Single Flanged Inlet
Material	Composite

Logistics

Carton Quantity	5
-----------------	---

Operational

Temperature Rating	• Maximum Continuous: 75° C • Minimum Continuous: -40° C w/o impact
--------------------	---

Product Assets

[Catalog \[English\]](#)