



# Locking Devices, Bryant Midget Locking, Industrial, Female Connector Body, 15A 125V, 2-Pole 3-Wire Grounding, ML-2R, Screw Terminal, Black & White

By Bryant  
Catalog # 7593NC



Locking Devices, Bryant Midget Locking, Industrial, Female Connector Body, 15A 125V, 2-Pole 3-Wire Grounding, ML-2R, Screw Terminal, Black & White.

## Features

Abuse resistant nylon housing

## General

Application	Heavy Duty Industrial
Catalog Number	7593NC
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	15A Midget Female Connector
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Style	Grounding
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body
UPC	781786671300

## Dimensions

Dimensions	1.25 in x 1.25 in x 2.15 in
Display Size	Midget NEMA Locking
Height	2.15 in
Length	1.25 in
Width	1.25 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current Rating	15 A
Voltage Rating	125 V
Voltage Rating Description	125 V

## Conductor Related

Conductor Range	#14 AWG
Number Of Wires	3-Wire
Number of Conductors	3-Wire Grounding
Wire Size	#18 AWG to #12 AWG

## Certifications And Compliance

Nema Rating	ML-2R
-------------	-------

## Logistics

Carton Quantity	10
Pallet Quantity	5850

## Product Assets

[Catalogs - Bryant Full Line Catalog](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
BRY\_CA-7593NC-SPEC-EN | REV 6/2024