



Power Protection Products, GFCI Circuit Breaker Sensing Modules, Industrial, Manual Set, 120V AC, GFCI Circuit Breakers, 4-6 mA Trip Level, Black

By Bryant
Catalog # [GFMD120M](#)



Power Protection Products, GFCI Circuit Breaker Sensing Modules, Industrial, Manual Set, 120V AC, GFCI Circuit Breakers, 4-6 mA Trip Level, Black.

General

Application	Heavy Duty Industrial Commercial
Catalog Number	GFMD120M
Color	Black
EU RoHS Indicator	No
Enclosure Type	Toggle
Environmental Conditions	NEMA 4X with Supplied Gasket
Item Type	Manual Set Sensing Module
Material	Composite
Number Of Poles	None
Operating Temperature	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Series	Industrial
Type	Manual Reset
UPC	781786450028

Dimensions

Height	2.4 in
Length	4.9 in

Electrical Ratings

Amperage Rating	1-50 A
Connectivity	None
Current / Amperage Rating	1-50 A
Frequency Rating	80% of Full Rating Continuous
Phase	60Hz
Trip Range	.025 Seconds in
Trip Type	Standard
Voltage Rating	120 VAC
Voltage Rating Description	120 VAC

Conductor Related

Wire Size	Terminal Screws
-----------	-----------------

Logistics

Carton Quantity	5
-----------------	---

Product Assets



A Hubbell brand