



Locking Devices, Industrial, Flanged Inlet, 20A 250V, 3-Pole 4-Wire Grounding, L14-20P, Screw Terminal, White

By Bryant
Catalog # [71420MB](#)



Locking Devices, Industrial, Flanged Inlet, 20A 125/250V AC, 3-Pole 4-Wire Grounding, L14-20P, Screw Terminal, White

Application

Extra Heavy Duty Industrial

General

Catalog Number	71420MB
Color	White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	20A Flanged Inlet
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Style	Equipment Base
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact
Type	Flanged Inlet
UPC	781786695160

Dimensions

Dimensions	3.06 in x 3.06 in x 2.03 in
Display Size	Standard Sized Product
Height	2.03 in

Length	3.06 in
Width	3.06 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current Rating	20 A
Dielectric Strength	Withstands 3000V Minimum
Voltage Rating	125/250 VAC
Voltage Rating Description	125/250V AC

Conductor Related

Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG

Certifications And Compliance

Nema Rating	L14-20P
-------------	---------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - Bryant Full Line Catalog](#)
[Specifications - 71420MB](#)

