



# Locking Devices, Industrial, Flanged Inlet, 20A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, L15-20P, Screw Terminal, With Weatherproof Cover



By Bryant  
Catalog # [71520MBWP](#)

Locking Devices, Industrial, Flanged Inlet, 20A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, L15-20P, Screw Terminal, White, With Weatherproof Cover

## Features

- Flanged Inlet
- 20A 3-Phase Delta 250V AC
- 3-Pole 4-Wire Grounding
- L15-20P
- Screw Terminal

## Application

Extra Heavy Duty Industrial

## General

Catalog Number	71520MBWP
Color	White
EU RoHS Indicator	Yes
Environmental Conditions	Weather Resistant
Insulation	Insulated Body
Item Type	20A Weather Protective Power Inlet
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Style	Weatherprotective
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact
Type	Flanged Inlet
UPC	781786695870

## Dimensions

Dimensions	2.88 in x 2.88 in x 2.02 in
Display Size	Standard Sized Product
Height	2.02 in
Length	2.88 in
Width	2.88 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current Rating	20 A
Dielectric Strength	Withstands 3000V Minimum in
Voltage Rating	3 Phase 250 VAC
Voltage Rating Description	3 Phase 250 VAC

## Conductor Related

Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG

## Certifications And Compliance

Nema Rating	L15-20P
-------------	---------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - 71520MBWP](#)