



Locking Devices, Bryant Power Interrupting, Industrial, Female Connector Body, 20A 125V/10A 250V DC 480V AC, Non-NEMA

By Bryant
Catalog # 23002G



Locking Devices, Bryant Power Interrupting, Industrial, Female Connector Body, 20A 125V/10A 250V DC 480V AC, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Black and White

Features

- Spring loaded safety shutter contains arcing when mating or un-mating devices under load
- Spring loaded safety shutter automatically ejects the plug eliminating contact teasing
- Box terminals in conjunction with screws with pressure pads provide maximum termination strength and dependability
- Three-piece clamp assembly provides maximum strain relief and protects against entry of moisture and dust

Application

Heavy Duty Industrial

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes

Conductor

Number Of Conductors	3-Wire Grounding
Number Of Wires	3-Wire
Wire Size	#16 AWG to #12 AWG
Number Of Poles	2-Pole
Conductor Range	#14 AWG to #12 AWG

Current

Amperage Rating	10A/20 A
Voltage Rating Description	125 VAC/125 VDC/250 VDC/480 VDC
Current/Amperage Rating Description	20 Amp/10 Amp
Current Rating	10A/20 A

Voltage Rating	125 VAC/125 VDC/250 VDC/480 VDC
Connectivity	Pressure Terminal Screws

Dimensions

Length	1.62 in
Display Size	Standard Sized Product
Height	3.56 in
Width	1.62 in
Dimensions	1.62 in x 1.62 in x 3.56 in

General

Color	Black, White
Style	Grounding
UPC	781786618831
Type	Connector Body
Material - Mounting Hardware	Cord Mounted
Insulation	Insulated Body
Item Type	10A/20A Connector
Material	Composite

Logistics

Carton Quantity	20
-----------------	----

Operational

Temperature Rating	• Maximum Continuous: 75° C • Minimum Continuous: -40° C w/o impact, -25° with impact.
--------------------	--

Product Assets

[Catalog \[English\]](#)