



# Locking Devices, Isolated Ground, Industrial, Flush Receptacle, 20A 250V, 2-Pole 3-Wire Grounding, L6-20R, Screw Terminal, Orange

By Bryant  
Catalog # 70620IG



Locking Devices, Isolated Ground, Industrial, Nylon Flush Receptacle, 20A 250V, 2-Pole 3-Wire Grounding, L6-20R, Screw Terminal, Orange.

### Features

- Limits electrical noise on the equipment grounding circuit by providing two grounding paths for the installation
- Nylon deep face design
- Triple-wipe brass line contacts
- Ground contacts and ground termination
- Nickel and brass plated wrap-around steel yoke

### General

Application	Extra Heavy Duty Industrial Specification Grade
Catalog Number	70620IG
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	20A Single Nylon Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Series	Locking
Style	Isolated Ground
Type	Single Receptacle
UPC	781786730816

### Dimensions

Dimensions	3.28 in x 1.70 in x 1.24 in
Display Size	Standard Sized Product
Height	1.24 in
Length	3.28 in
Width	1.7 in

### Electrical Ratings

Amperage Rating	20 A
Connectivity	Terminal Screws
Current Rating	20 A
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250V

### Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #8 AWG

### Certifications And Compliance

Nema Rating	L6-20R
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRY\_CA-70620IG-SPEC-EN | REV 6/2024