



AT22A19A30GS

by Burndy
Catalog ID: AT22A19A30GS

Substation Connectors

Product Details

General

Application	Substation
Connector Type	A-Frame
Installation Torque Recommended Run in-lb	660 LBS/in
Installation Torque Recommended Tap in-lb	660 LBS/in
Material	Aluminum Alloy
Material - Hardware	Aluminum
One Wrench Installation	Y
Physical Attribute - Number of Run Conductors	1
Physical Attribute - Number of Tap Conductors	2
Physical Attribute - Pad Orientation	30 Degree
Plated	N
Plating Type	Unplated
UPC	621945233645
UPC 12 Digit	6219452336455

Dimensions

Connector Angle	30 Degree
Dimension - B Length inch	6.00 in
Dimension - Height inch	11.23 in
Dimension - L Length Overall mm	301 mm
Dimension - Length BB inch	4.50 in
Dimension - Length Overall inch	11.87 in

Electrical Ratings

Rating - KVA	230 kV
--------------	--------

Conductor Related

Conductor - AL Tube Std Run	4 IPS
Conductor - AL Tube Std Run Range	4 IPS
Conductor - AL Tube Std Tap	2 1/2 IPS
Conductor - AL Tube Std Tap Range	2 1/2 IPS

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)