



# AT22A20A30

by Burndy  
Catalog ID: AT22A20A30

Prop 65 Notice

Substation Connectors

## Product Details

### General

Application	Substation
Connector Type	A-Frame
Installation Torque Recommended Run in-lb	480 lb-in
Installation Torque Recommended Tap in-lb	480 lb-in
Material	Aluminum Alloy, Cast
Material - Hardware	Aluminum Alloy
Physical Attribute - Number of Run Conductors	1
Physical Attribute - Number of Tap Conductors	2
Physical Attribute - Pad Orientation	30 Degree
Plated	N
Plating Type	Unplated
UPC	781810286791
UPC 12 Digit	7818102867911

### Dimensions

Connector Angle	30 Degree
Dimension - B Length inch	6.00 in
Dimension - Height inch	13.12 in
Dimension - L Length Overall mm	315 mm
Dimension - Length BB inch	5.00 in
Dimension - Length Overall inch	12.42 in

### Electrical Ratings

Rating - KVA	230 kV
--------------	--------

### Conductor Related

Conductor - AL Tube Std Run	4 IPS
Conductor - AL Tube Std Run Range	4 IPS
Conductor - AL Tube Std Tap	3 IPS
Conductor - AL Tube Std Tap Range	3 IPS

### Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

## Logistics

Minimum Pack Quantity	6
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)