



AT24A19A30SS

by Burndy
Catalog ID: AT24A19A30SS

Substation Connectors

Product Details

General

Application	Substation
Connector Type	A-Frame
Installation Torque Recommended Run in-lb	660 lb-in
Installation Torque Recommended Tap in-lb	660 lb-in
Material	Aluminum Alloy, Cast
Material - Hardware	Stainless Steel
One Wrench Installation	Y
Physical Attribute - Number of Run Conductors	1
Physical Attribute - Number of Tap Conductors	2
Physical Attribute - Pad Orientation	30 Degree
Plated	N
Plating Type	Unplated
UPC	621945336773
UPC 12 Digit	6219453367733

Dimensions

Connector Angle	30 Degree
Dimension - B Length inch	6.00 in
Dimension - Height inch	12.15 in
Dimension - L Length Overall mm	338 mm
Dimension - Length BB inch	4.50 in
Dimension - Length Overall inch	13.32 in

Electrical Ratings

Rating - KVA	230 kV
--------------	--------

Conductor Related

Conductor - AL Tube Std Run	5 IPS
Conductor - AL Tube Std Run Range	5 IPS
Conductor - AL Tube Std Tap	2 1/2 IPS
Conductor - AL Tube Std Tap Range	2 1/2 IPS

Certifications and Compliance

Standards - RoHS Compliance Status	UI
------------------------------------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)