



B1614

by Burndy
Catalog ID: B1614

Mold, Horizontal Cable Tap to Horizontal Cast Iron Surface, 6 AWG, 25Cl Weld Metal.

Features: Type BCS-5 Molds Are Used To Join Horizontal Cable Taps To Horizontal Cast Iron Surfaces, Note That The Cable Is ON The Surface, Size Range Is 6 AWG Through 1 AWG Concentric Stranded Copper Conductors, Includes: Frame, B38-0309-00 Flint Ignitor, Conductor Type: Concentric Stranded Copper, Cartridge Type: Cast Iron, Recommended Accessories: B38-3922-00 Mold Cleaning Brush, B38-0135-00 Cable Cleaning Brush, B38-0101-00 Rasp

Product Details

General

Application	For Joining Horizontal Cable Taps To Horizontal Cast Iron Surfaces
Sub Brand	BURNDYWELD
Type	Molds
UPC	781810392713
UPC 12 Digit	7818103927133

Conductor Related

Conductor - Copper Str Size	6 AWG
Conductor - Copper Str Size Range	6 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)