



AT20A20A20GS

by Burndy
Catalog ID: AT20A20A20GS

Prop 65 Notice

Substation Connectors

Product Details

General

Application	Substation
Connector Type	A-Frame
Installation Torque Recommended Run in-lb	660 LBS/in
Installation Torque Recommended Tap in-lb	660 LBS/in
Material	Aluminum Alloy
Material - Hardware	Aluminum
One Wrench Installation	Y
Physical Attribute - Number of Run Conductors	1
Physical Attribute - Number of Tap Conductors	2
Physical Attribute - Pad Orientation	20 Degree
Plated	N
Plating Type	Unplated
UPC	781810468401
UPC 12 Digit	7818104684011

Dimensions

Connector Angle	20 Degree
Dimension - B Length inch	5.00 in
Dimension - Height inch	11.56 in
Dimension - L Length Overall mm	291 mm
Dimension - Length BB inch	5.00 in
Dimension - Length Overall inch	11.44 in

Electrical Ratings

Rating - KVA	230 kV
--------------	--------

Conductor Related

Conductor - AL Tube Std Run	3 IPS
Conductor - AL Tube Std Run Range	3 IPS
Conductor - AL Tube Std Tap	3 IPS
Conductor - AL Tube Std Tap Range	3 IPS

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)