



B2154

by Burndy Catalog ID: B2154

Mold, Horizontal Through Cable to Ground Rod, 4 AWG, 90 Weld Metal, 1/2" Ground Rod.

Features: Type BCR-3 Molds Are Used To Join Horizontal Through Run Cable To The Side Of A Vertical Ground Rod, Size Range Is 6 AWG Through 1000 KCMIL Concentric Stranded Copper Conductors, 1/2 IN Through 1 IN For The Ground Rod, Ground Rod Size: 1/2 IN, Conductor Type: Concentric Stranded Copper, Cartridge Type: Standard, Recommended Accessories: B38-3922-00 Mold Cleaning Brush, B38-0135-00 Cable Cleaning Brush, B38-0330-00 Cable Clamp, B38-0304-00 File, Required Tools: B38-0309-00 Flint Ignitor

Product Details

General

Application	For Joining Horizontal Through Run Cable To The Side Of A Vertical Ground Rod
Sub Brand	BURNDYWELD
Trade Name	BURNDYWeld®
Туре	Molds
UPC	781810492710
UPC 12 Digit	7818104927100

Conductor Related

Conductor - Copper Str Tap	4 AWG
Conductor - Rod Size	1/2 in
Conductor Type	CU C Str-TapRod-Size

Certifications and Compliance

Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175

1-603-647-5299 (International)