



AT20ACG4

by Burndy
Catalog ID: AT20ACG4

Angled V Substation Connectors

Product Details

General

Application	Substation
Connector Type	A-Frame
Installation Torque Recommended Run in-lb	660 IN LBS(75 Nm)
Material	Aluminum Alloy, Cast
Material - Hardware	Aluminum Alloy
Physical Attribute - Number of Run Conductors	1
Physical Attribute - Number of Tap Conductors	2
Physical Attribute - Pad Orientation	20 Degree
Plated	N
Plating Type	Unplated
UPC	621945109193
UPC 12 Digit	6219451091933

Dimensions

Connector Angle	20 Degree
Dimension - B Length inch	5.00 in
Dimension - Height inch	10.67 in
Dimension - L Length Overall mm	271 mm
Dimension - Length BB inch	4.25 in
Dimension - Length Overall inch	10.24 in
Dimension - Width inch	5 in

Electrical Ratings

Rating - KVA	230 kV
--------------	--------

Conductor Related

Conductor - AL Tube EH Run	3 " IPS Alum Tube
Conductor - AL Tube Std Tap	2 " IPS Alum Tube

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)