



## B1332

by Burndy  
Catalog ID: B1332

Mold, Horizontal Parallel through Cables, 4/0 AWG (Run), 3/0 AWG (Tap), 200 Weld Metal.

Features: BCC-7 Type Molds Are Used To Join Horizontal Parallel Through Run Cables, One Cable Runs Above The Other Cable In The Mold, Size Range Is 6 AWG Through 4/0 AWG Concentric Stranded Copper Conductors, Recommended Accessories: B38-3922-00 Mold Cleaning Brush, B38-0135-00 Cable Cleaning Brush, B38-0330-00 Cable Clamp, Conductor Type: Concentric Stranded Copper, Required Tools: B38-0309-00 Flint Ignitor, Cartridge Type: Standard

## Product Details

### General

|              |  |
|--------------|--|
| Application  | For Joining Horizontal Parallel Through Run Cables |
| Sub Brand    | BURNDYWELD   |
| Type         | Molds  |
| UPC          | 781810382943                                       |
| UPC 12 Digit | 7818103829433                                      |

### Conductor Related

|                                  |  |
|----------------------------------|--|
| Conductor - Copper Str Run       | 4/0 AWG  |
| Conductor - Copper Str Run Range | 4/0 AWG  |
| Conductor - Copper Str Tap       | 3/0 AWG  |
| Conductor - Copper Str Tap Range | 3/0 AWG  |
| Conductor Type                   | <ul style="list-style-type: none"> <li>• CU C Str-Run</li> <li>• CU C Str-Tap</li> </ul> |

### Certifications and Compliance

|                                    |    |
|------------------------------------|----|
| Standards - RoHS Compliance Status | CM |
|------------------------------------|----|

### Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)