



## B2487

by Burndy  
Catalog ID: B2487

Mold, Angular Cable Drop to Vertical Steel Pipe, 1/0 AWG, 4" to 6" Pipe, 90 Weld Metal.

Features: Type BCS-3 Molds Are Used To Join The End Of A Copper Cable At A 45 DEG Angle To A Vertical Steel Surface, Size Range Is 6 AWG Through 1000 KCMIL Concentric Stranded Copper Conductors, Cable To Pipe Connection, Conductor Type: Concentric Stranded Copper, Recommended Accessories: B106-32 Vertical Chain Clamp With B-106 Handles For 4 IN Pipe And Smaller, B40-0106-27 20 Chain Extension For 4 IN To 10 IN Pipe, B38-3922-00 Mold Cleaning Brush, B38-0135-00 Cable Cleaning Brush, B38-0101-00 Rasp, Required Tools: B38-0309-00 Flint Ignitor, Pipe Size: 4 - 6 IN, Cartridge Type: Standard

## Product Details

### General

Application	For Joining End Of A Copper Cable At A 45 DEG Angle To A Vertical Steel Surface
Sub Brand	BURNDYWELD
Type	Molds
UPC	781810393437
UPC 12 Digit	7818103934377

### Conductor Related

Conductor - Copper Str Size	1/0
Conductor - Copper Str Size Range	1/0
Conductor - Rigid Pipe Size	4 in;5 in;6 in
Conductor - Rigid Pipe Size Range	4 in-6 in
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Str-Size</li> <li>• Pipe Rigid-Size</li> </ul>

### Certifications and Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)