



## B24G844NTN

by Burndy  
Catalog ID: B24G844NTN

Prop 65 Notice

Tin Plated Ferrules

## Product Details

### General

|                                       |               |
|---------------------------------------|---------------|
| Connector Type                        | Braid         |
| Material                              | Copper        |
| Material - Ferrules                   | Y             |
| Physical Attribute - Number of Braids | 8             |
| Plated                                | Y             |
| UPC                                   | 781810450062  |
| UPC 12 Digit                          | 7818104500622 |

### Dimensions

|                                 |          |
|---------------------------------|----------|
| Dimension - D inch              | 3        |
| Dimension - Hole Size inch      | 0.56     |
| Dimension - L Length Overall mm | 2134 mm  |
| Dimension - Length Overall inch | 84.00 in |
| Dimension - N inch              | 0.62     |
| Dimension - Pad Width inch      | 3        |

### Electrical Ratings

|                           |      |
|---------------------------|------|
| Rating - Outdoor Amperage | 2000 |
|---------------------------|------|

### Certifications and Compliance

|                                    |    |
|------------------------------------|----|
| Certification - CSA Approved       | No |
| Certification - ETL                | No |
| Certification - UL Recognized      | No |
| Certification - cULus              | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed                          | No |

## Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)