



## B542

by Burndy  
Catalog ID: B542

Mold, Horizontal Cable through Top Of Ground Rod, 4/0 AWG, 115 Weld Metal, 1/2" Ground Rod.

Features: Type BCR-2 Molds Are Used To Join Horizontal Through Copper Cable To The Top Of A Vertical Ground Rod, Size Range Is 6 AWG Through 1000 KCMIL Concentric Stranded Copper Conductors, 1/2 IN Through 1 IN For The Ground Rod, Conductor Type: Concentric Stranded Copper, Ground Rod Size: 1/2 IN, Cartridge Type: Standard, Recommended Accessories: B38-3922-00 Mold Cleaning Brush, B38-0135-00 Cable Cleaning Brush, B38-0304-00 File, B38-0330-00 Cable Clamp

## Product Details

### General

Application	For Joining Horizontal Through Copper Cable To The Top Of A Vertical Ground Rod
Sub Brand	BURNDYWELD
Type	Molds
UPC	781810385098
UPC 12 Digit	7818103850988

### Conductor Related

Conductor - Copper Str Tap	4/0 AWG
Conductor - Copper Str Tap Range	4/0 AWG
Conductor - Rod Size	1/2 in
Conductor - Rod Size Range	1/2 in
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Str-Tap</li> <li>• Rod-Size</li> </ul>

### Certifications and Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

### Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)