



B539

by Burndy
Catalog ID: B539

Mold, Horizontal Cable through Top of Ground Rod, 1/0 AWG, 90 Weld Metal, 1/2" Ground Rod.

Features: Type BCR-2 Molds Are Used To Join Horizontal Through Copper Cable To The Top Of A Vertical Ground Rod, Size Range Is 6 AWG Through 1000 KCMIL Concentric Stranded Copper Conductors, 1/2 IN Through 1 IN For The Ground Rod, Conductor Type: Concentric Stranded Copper, Ground Rod Size: 1/2 IN, Recommended Accessories: B38-3922-00 Mold Cleaning Brush, B38-0135-00 Cable Cleaning Brush, B38-0304-00 File, B38-0330-00 Cable Clamp, Cartridge Type: Standard

Product Details

General

Application	For Joining Horizontal Through Copper Cable To The Top Of A Vertical Ground Rod
Sub Brand	BURNDYWELD
Type	Molds
UPC	781810384978
UPC 12 Digit	7818103849788

Conductor Related

Conductor - Copper Str Tap	1/0
Conductor - Copper Str Tap Range	1/0
Conductor - Rod Size	1/2 in
Conductor - Rod Size Range	1/2 in
Conductor Type	• CU C Str-Tap • Rod-Size

Certifications and Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)