



## B551

by Burndy  
Catalog ID: B551

Mold, Horizontal Cable through Top of Ground Rod, 250 kcmil, 150 Weld Metal, 5/8" Ground Rod.

Features: Type BCR-2 Molds Are Used To Join Horizontal Through Copper Cable To The Top Of A Vertical Ground Rod, Size Range Is 6 AWG Through 1000 KCMIL Concentric Stranded Copper Conductors, 1/2 IN Through 1 IN For The Ground Rod, Ground Rod Size: 5/8 IN, Conductor Type: Concentric Stranded Copper, Recommended Accessories: B38-3922-00 Mold Cleaning Brush, B38-0135-00 Cable Cleaning Brush, B38-0304-00 File, B38-0330-00 Cable Clamp, Cartridge Type: Standard

## Product Details

### General

|              |   |
|--------------|---|
| Application  | For Joining Horizontal Through Copper Cable To The Top Of A Vertical Ground Rod |
| Sub Brand    | BURNDYWELD  |
| Trade Name   | BURNDYWeld®   |
| Type         | Molds   |
| UPC          | 781810385463  |
| UPC 12 Digit | 7818103854633   |

### Conductor Related

|                            |  |
|----------------------------|--|
| Conductor - Copper Str Tap | 250 kcmil  |
| Conductor - Rod Size       | 5/8 in   |
| Conductor Type             | <ul style="list-style-type: none"> <li>• CU C Str-Tap</li> <li>• Rod-Size</li> </ul> |

### Certifications and Compliance

|                                    |     |
|------------------------------------|-----|
| Standards - RoHS Compliance Status | CM  |
| UL Listed                          | Yes |

### Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)