



## B5667

by Burndy  
Catalog ID: B5667

Mold, Horizontal Parallel Run Cables through Top of Ground Rod, 2 AWG, 115 Weld Metal, 1/2" Ground Rod.

Features: Type BCR-24 Molds Are Used To Join Horizontal Parallel Cables To The Top Of A Vertical Ground Rod, Size Range Is 4 AWG Through 750 KCMIL Concentric Stranded Copper Conductors, 1/2 IN Through 1 IN For The Ground Rod, Ground Rod Size: 1/2 IN, Conductor Type: Concentric Stranded Copper, Cartridge Type: Standard, Recommended Accessories: B38-3922-00 Mold Cleaning Brush, B38-0135-00 Cable Cleaning Brush, B38-0330-00 Cable Clamp, B38-0304-00 File, Required Tools: B38-0309-00 Flint Ignitor

## Product Details

### General

|              |  |
|--------------|--|
| Application  | For Joining Horizontal Parallel Cables To The Top Of A Vertical Ground Rod |
| Sub Brand    | BURNDYWELD   |
| Type         | Molds  |
| UPC          | 781810389683   |
| UPC 12 Digit | 7818103896833  |

### Conductor Related

|                            |  |
|----------------------------|--|
| Conductor - Copper Str Tap | 2 AWG  |
| Conductor - Rod Size       | 1/2 in   |
| Conductor Type             | <ul style="list-style-type: none"> <li>• CU C Str-Tap</li> <li>• Rod-Size</li> </ul> |

### Certifications and Compliance

|                                    |    |
|------------------------------------|----|
| Standards - RoHS Compliance Status | CM |
|------------------------------------|----|

### Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)