



## B5680

by Burndy  
Catalog ID: B5680

Mold, Horizontal Parallel through Cables, 3/0 AWG (Run), 8 AWG (Tap), 90 Weld Metal.

Features: BCC-7 Type Molds Are Used To Join Horizontal Parallel Through Run Cables, One Cable Runs Above The Other Cable In The Mold, Size Range Is 6 AWG Through 4/0 AWG Concentric Stranded Copper Conductors, Recommended Accessories: B38-3922-00 Mold Cleaning Brush, B38-0135-00 Cable Cleaning Brush, B38-0330-00 Cable Clamp, Conductor Type: Concentric Stranded Copper, Cartridge Type: Standard, Required Tools: B38-0309-00 Flint Ignitor

## Product Details

### General

Application	For Joining Horizontal Parallel Through Run Cables
Sub Brand	BURNDYWELD
Type	Molds
UPC	781810386200
UPC 12 Digit	7818103862000

### Conductor Related

Conductor - Copper Str Run	3/0 AWG
Conductor - Copper Str Run Range	3/0 AWG
Conductor - Copper Str Tap	8 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Str-Run</li> <li>• CU C Str-Tap</li> </ul>

### Certifications and Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)