



B622

by Burndy
Catalog ID: B622

Mold, Horizontal Through Cable to Horizontal Steel Surface, 350 kcmil, 250 Weld Metal.

Features: Type BCS-2 Molds Are Used To Join Horizontal Through Copper Cable To Any Horizontal Steel Surface, Note The Cable Is Off The Surface, Size Range Is 1/0 AWG Through 1000 KCMIL Concentric Stranded Copper Conductors, Recommended Accessories: B38-3922-00 Mold Cleaning Brush, B38-0135-00 Cable Cleaning Brush, B38-0101-00 Rasp, Conductor Type: Concentric Stranded Copper, Cartridge Type: Standard, Required Tools: B38-0309-00 Flint Ignitor

Product Details

General

Application	For Joining Horizontal Through Copper Cable To Any Horizontal Steel Surface
Sub Brand	BURNDYWELD
Type	Molds
UPC	781810391327
UPC 12 Digit	7818103913277

Conductor Related

Conductor - Copper Str Size	350 kcmil
Conductor Type	CU C Str-Size

Certifications and Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)