



B594

by Burndy
Catalog ID: B594

Mold, Angular Cable Drop to Vertical Steel Surface, 250 kcmil, 115 Weld Metal.

Features: Type BCS-3 Molds Are Used To Join The End Of A Copper Cable At A 45 DEG Angle To A Vertical Steel Surface, Size Range Is 6 AWG Through 1000 KCMIL Concentric Stranded Copper Conductors, Cable To Flat Steel, Recommended Accessories: Magnetic Clamps To Hold Molds Against Vertical Steel, B38-3922-00 Mold Cleaning Brush, B38-0135-00 Cable Cleaning Brush, B38-0101-00 Rasp, Conductor Type: Concentric Stranded Copper, Cartridge Type: Standard, Required Tools: B38-0309-00 Flint Ignitor

Product Details

General

| | |
|--------------|---|
| Application | For Joining End Of A Copper Cable At A 45 DEG Angle To A Vertical Steel Surface |
| Sub Brand | BURNDYWELD |
| Type | Molds |
| UPC | 781810394069 |
| UPC 12 Digit | 7818103940699 |

Conductor Related

| | |
|-----------------------------|--|
| Conductor - Copper Str Size | 250 kcmil |
| Conductor Type | <ul style="list-style-type: none"> • CU C Str-Size • Pipe Rigid-Size |

Certifications and Compliance

| | |
|------------------------------------|-----|
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)