



B7508

by Burndy
Catalog ID: B7508

Mold, Horizontal Parallel Tap to Rebar, 6 AWG, #4 & Larger Rebar, 25 Weld Metal.

Features: Type BCRE-1 Molds Are Recommended For Parallel, Horizontal Connections For Concentric Stranded Conductors 6 AWG Through 4/0 AWG Joined To Reinforcing Bars 3 AWG Through 6 AWG And Larger, The High Copper Content Joint Has A Higher Current Carrying Capacity Than The Conductors Being Joined And Is Impervious To Vibration And Moisture, Cartridge Type: Standard, Required Tools: B38-0309-00 Flint Ignitor, Conductor Type: Concentric Stranded Copper, Includes: Frame, Packing Material: B38406100 Ceramic Fiber, Recommended Accessories: B38-3922-00 Mold Cleaning Brush, B38-0135-00 Cable Cleaning Brush, B38-0304-00 File, Rebar Size: #4 And Larger

Product Details

General

Application	For Parallel, Horizontal Connections
Sub Brand	BURNDYWELD
Trade Name	BURNDYWeld®
Type	Molds
UPC	781810407752
UPC 12 Digit	7818104077522

Conductor Related

Cable Size	#4
Conductor - Copper Str Size	6 AWG
Conductor - Copper Str Size Range	6 AWG
Conductor - Rebar Size	#4 or Larger
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • Rebar-Size

Certifications and Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)