



B7600

by Burndy
Catalog ID: B7600

Mold, Horizontal Cable Tap to Horizontal Rebar Run, 1/0 AWG, #4 Rebar, 90 Weld Metal.

Features: Type BCRE-2 Molds Are Recommended For Right Angle, Horizontal Connections For Concentric Stranded Conductors 6 AWG Through 4/0 AWG Joined To Reinforcing Bars 3 AWG Through 6 AWG, The High Copper Content Joint Has A Higher Current Carrying Capacity Than The Conductors Being Joined And Is Impervious To Vibration And Moisture, Cartridge Type: Standard, Conductor Type: Concentric Stranded Copper, Recommended Accessories: B40-0319-03 Mold Cleaner For Cartridge Sizes #90 - #500, B38-3922-00 Mold Cleaning Brush, B38-0135-00 Cable Cleaning Brush, B38-0304-00 File, Packing Material: B38032900 Copper Shim Stock, Rebar Size: #4, Required Tools: B38-0309-00 Flint Ignitor

Product Details

General

Application	For Right Angle, Horizontal Connections For Solid Or Concentric Stranded Conductors
Sub Brand	BURNDYWELD
Trade Name	BURNDYWeld®
Type	Molds
UPC	781810408490
UPC 12 Digit	7818104084900

Conductor Related

Conductor - Copper Str Size	1/0
Conductor - Copper Str Size Range	1/0
Conductor - Rebar Size	4
Conductor - Rebar Size Range	4
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • Rebar-Size

Certifications and Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)