



B7726

by Burndy
Catalog ID: B7726

Mold, Horizontal through Cable to Horizontal Rebar, 2 AWG, #5 Rebar, 90 Weld Metal.

Features: Type BCRE-4 Molds Are Recommended For Horizontal Through Conductors To Horizontal Rebar At Right Angle Connections For Concentric Stranded Conductors 6 AWG Through 4/0 AWG Joined To Reinforcing Bars #3 Through #6 And Larger, The High Copper Content Joint Has A Higher Current Carrying Capacity Than The Conductors Being Joined And Is Impervious To Vibration And Moisture, Cartridge Type: Standard, Conductor Type: Concentric Stranded Copper, Recommended Accessories: B40-0319-03 Mold Cleaner For Cartridge Sizes #90 - #500, B38-3922-00 Mold Cleaning Brush, B38-0135-00 Cable Cleaning Brush, B38-0304-00 File, Required Tools: B38-0309-00 Flint Ignitor, Packing Material: B38032900 Copper Shim Stock, Rebar Size: #5

Product Details

General

| | |
|--------------|--|
| Application | For Horizontal Through Conductors To Horizontal Rebar At Right Angle Connections |
| Sub Brand | BURNDYWELD |
| Trade Name | BURNDYWeld® |
| Type | Molds |
| UPC | 781810410080 |
| UPC 12 Digit | 7818104100800 |

Conductor Related

| | |
|-----------------------------------|---|
| Cable Size | #2 |
| Conductor - Copper Str Size | 2 AWG |
| Conductor - Copper Str Size Range | 2 AWG |
| Conductor - Rebar Size | #5 |
| Conductor - Rebar Size Range | 5 |
| Conductor Type | <ul style="list-style-type: none"> • CU C Str-Size • Rebar-Size |

Certifications and Compliance

| | |
|------------------------------------|----|
| Standards - RoHS Compliance Status | CM |
|------------------------------------|----|

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)

