



## B7720

by Burndy  
Catalog ID: B7720

Mold, Horizontal through Cable to Horizontal Rebar, 1/0 AWG, #4 Rebar, 115 Weld Metal.

Features: Type BCRE-4 Molds Are Recommended For Horizontal Through Conductors To Horizontal Rebar At Right Angle Connections For Concentric Stranded Conductors 6 AWG Through 4/0 AWG Joined To Reinforcing Bars #3 Through #6 And Larger, The High Copper Content Joint Has A Higher Current Carrying Capacity Than The Conductors Being Joined And Is Impervious To Vibration And Moisture, Cartridge Type: Standard, Recommended Accessories: B40-0319-03 Mold Cleaner For Cartridge Sizes #90 - #500, B38-3922-00 Mold Cleaning Brush, B38-0135-00 Cable Cleaning Brush, B38-0304-00 File, Conductor Type: Concentric Stranded Copper, Rebar Size: #4, Packing Material: B38032900 Copper Shim Stock, Required Tools: B38-0309-00 Flint Ignitor

## Product Details

### General

Application	For Horizontal Through Conductors To Horizontal Rebar At Right Angle Connections
Sub Brand	BURNDYWELD
Trade Name	BURNDYWeld®
Type	Molds
UPC	781810409961
UPC 12 Digit	7818104099611

### Conductor Related

Cable Size	1/0 AWG
Conductor - Copper Str Size	1/0
Conductor - Copper Str Size Range	1/0
Conductor - Rebar Size	#4
Conductor - Rebar Size Range	4
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Str-Size</li> <li>• Rebar-Size</li> </ul>

### Certifications and Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

### Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)

