



## BD108CG2

by Burndy  
Catalog ID: BD108CG2

### Flexible Copper Braid

Designed to house a variety of electronic control or instrumentation devices. Consolets provide protection from dust, dirt, oil and water. Flexible design allows for mounting on either or two sides, creating control surfaces of 30 degrees or 60 degrees. Consolets can be mounted on desktops, pedestals or other flat surfaces. Bodies and doors fabricated from 14 gauge 304 stainless steel. Continuously welded seams ground smooth, less knockouts or holes. Captive cover screws thread into sealed wells. Control panel is continuously hinged along bottom edge. Closed cell oil resistant neoprene gasket. Grounding provisions included.

## Product Details

### General

Application	Designed to house a variety of electronic control or instrumentation devices. Consolets provide protection from dust, dirt, oil, and water. Flexible design allows for mounting on either of two sides, creating control surfaces of 30 degrees or 60 degrees.
Construction	Continuously Welded Seams
Cover Type	Screw Cover
Knockouts	No
Listings	UL, CSA
Material	Copper Stainless Steel
Physical Attribute - Number of Braids	1
Plated	Y
Plating Type	Tin
Series	WC-SS
Type	Console
UPC	786725849437

### Dimensions

Actual Depth	7.09 in
Height	8 in
Weight	14 lb
Width	16 in

### Electrical Ratings

Rating - Indoor Amperage	190
Rating - Outdoor Amperage	225

### Certifications and Compliance

Certification - CSA Approved	Yes
------------------------------	-----

Certified Listed	cULus
Industry Standard(s)	UL467
Nema Rating	12
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	UI
UL Listed	Yes

**Logistics**

Carton Quantity	1
Minimum Pack Quantity	1

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
 47 East Industrial Park Drive  
 Manchester, New Hampshire 03109

**Customer Service Hours:**  
 8 AM - 8 PM Eastern Monday-Friday  
 Emergency Service 24-hours/365 Days  
 Phone: 1-800-346-4175  
 1-603-647-5299 (International)