

# BYNA39RTHACCC

by Burndy  
Catalog ID: Byna39RTHACCC

Prop 65 Notice

HYLUG™ Terminal Pad Assembly (ACCC) with TMH24 Hardware Kit, 713 kcmil, 330mm<sup>2</sup>, 380mm<sup>2</sup> ACCC, 230kV



## Product Details

### General

Connector Type	Terminal
Die Index	722
Installation Torque Recommended in-lb	300 in-lb
Material	Aluminum
Trade Name	HYLUG™
UPC	781810506660
UPC 12 Digit	7818105066600

### Dimensions

Dimension - D inch	4.50 in
Dimension - Hole Size inch	0.56 in
Dimension - Inside Diameter inch	0.97 in
Dimension - L Length Overall mm	411 mm
Dimension - Length Overall inch	16.2 in
Dimension - Outside Diameter inch	1.50 in
Dimension - Pad Width inch	3.25 in
Physical Attribute - Tongue Angle	Straight

### Conductor Related

Conductor - ACCC Str Size	713 kcmil(Dove);330mm <sup>2</sup> (Oslo);380mm <sup>2</sup> (Amsterdam)
---------------------------	--

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)