

BYNA43R15HHT

by Burndy
Catalog ID: BYNA43R15HHT

Prop 65 Notice

BURNDY; HYLUG; BYNA-R-HHT, Kit; Features: Single pad Full tension compression deadend for 250 Deg C rated ACSS transmission lines up to and including 230kV; Standard 15 Deg NEMA tap pad provides either 0 Deg or 30 Deg tap when BYNA-R15 terminal is used; with Hardware; For ACSS Conductor; RoHS Under Investigation.



Product Details

General

Connector Type	Terminal
Die Index	724
Feature - Barrel Style	Tapered
Feature - Barrel Type	Long
Material	Aluminum
Physical Attribute - Number of Holes	4
UPC	781810514283
UPC 12 Digit	7818105142833

Dimensions

Dimension - Bolt Size fraction	1/2
Dimension - D inch	3.95 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	14.41 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	1.61 in
Dimension - Pad Width inch	3.07 in
Dimension - Thread Size	1/2
Physical Attribute - Tongue Angle	15 Degree

Conductor Related

Conductor - ACSS Str Size	605 (24/7) kcmil;605 (26/7) kcmil;605 (30/7) kcmil;605 (30/19) kcmil;636 (20/7) kcmil;636 (22/7) kcmil;636 (24/7) kcmil;636 (26/7) kcmil;636 (30/7) kcmil;636 (30/19) kcmil;666.6 (24/7) kcmil;666.6 (26/7) kcmil
Conductor - ACSS Str Size Range	605 (24/7) kcmil-666.6 (26/7) kcmil

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)