

BYNA43RT15ACCC

by Burndy
Catalog ID: BYNA43RT15ACCC

HYLUG™ Terminal Pad Assembly (ACCC), 816 kcmil-430mm² ACCC, 15⁰, 230kV



Product Details

General

Connector Type	Terminal
Die Index	724
Feature - Barrel Style	Tapered
Installation Torque Recommended in-lb	300 in-lb
Material	Aluminum
Physical Attribute - Number of Holes	4
Trade Name	HYLUG™
UPC	781810514313
UPC 12 Digit	7818105143133

Dimensions

Dimension - Bolt Size fraction	1/2
Dimension - D inch	4.5 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Hole Size inch	0.56 in
Dimension - Inside Diameter inch	1.05 in
Dimension - Length Overall inch	16.2 in
Dimension - N inch	1.12 in
Dimension - Outside Diameter inch	1.61 in
Dimension - Pad Width inch	3.25 in
Dimension - Thread Size	1/2
Physical Attribute - Tongue Angle	15 Degree

Conductor Related

Conductor - ACCC Str Size	816 kcmil(Grosbeak);430mm ² (Brussels)
Conductor - ACCC Str Size Range	816 kcmil(Grosbeak)-430mm ² (Brussels)

Certifications and Compliance

Standards - RoHS Compliance Status	UI
------------------------------------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)