

DUW28AE

by Burndy
Catalog ID: DUW28AE

Prop 65 Notice

Al Alloy Deadend Strain Clamp, With Pulling Eye, #1 - 4/0 AWG Al, #2 - 4/0 AWG ACSR



Product Details

General

Connector Type	Deadend
Material	Aluminum Alloy
Material - Hardware	Galvanized Steel
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
UPC	781810013380

Dimensions

Dimension - B Length fraction	5-4/21 in
Dimension - B Length inch	5.19 in
Dimension - Height fraction	2-3/50 in
Dimension - Height inch	2.06 in
Dimension - Hole Size fraction	22/25
Dimension - Hole Size inch	0.88 in
Dimension - Hole Size mm	22 mm
Dimension - L Length Overall mm	264 mm
Dimension - Length Overall inch	10.41 in
Dimension - Width fraction	2-1/4 in
Dimension - Width inch	2.25 in
Dimension - Width mm	57 mm
Dimension - Z inch	1.44 in

Conductor Related

Conductor - AAAC 5005 Size	77.47 (7) kcmil;123.3 (7) kcmil;155.4 (7) kcmil;195.7 (7) kcmil;246.9 (7) kcmil
Conductor - AAAC 5005 Size Range	77.47 (7) kcmil-246.9 (7) kcmil
Conductor - AAAC 6201 Size	77.47 (7) kcmil;123.3 (7) kcmil;155.4 (7) kcmil;195.7 (7) kcmil;246.9 (7) kcmil
Conductor - AAAC 6201 Size Range	77.47 (7) kcmil-246.9 (7) kcmil
Conductor - ACSR Str Size	2 (6/1) Sparrow AWG;2 (7/1) Sparate AWG;1 (6/1) Robin AWG;1/0 (6/1) Raven AWG;2/0 (6/1) Quail AWG;3/0 (6/1) Pigeon AWG;4/0 (6/1) Penquin AWG
Conductor - ACSR Str Size Range	2 (6/1) Sparrow AWG-4/0 (6/1) Penquin AWG

Conductor - AL Str Size	1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - AL Str Size Range	1 AWG-4/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)