

# BYNA32RT15HACCCGS

by Burndy  
Catalog ID: BYNA32RT15HACCCGS

Prop 65 Notice

HYLUG™ TERMINAL With Hardware Kit TMH338, CTC NO. 600-153-1, Accomodates LINNET 431 Kcmil, ORIOLE 438 Kcmil, COPENHAGEN 230mm<sup>2</sup>, REYKJAVIK 235mm<sup>2</sup> ACCC®, DIE Index 717, 15 Degree Barrel Angle



## Product Details

### General

Application	For ACCC Conductor, Corona free operation up to 230 KV
Connector Type	Terminal
Die Index	717
Die Type	S717, P717, L717W
Feature - Barrel Style	Tapered
Installation Torque Recommended in-lb	480 in-lb
Material	Aluminum
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Orientation	15 Degree
Prefilled Oxide Inhibitor	N
Trade Name	HYLUG™
UPC	781810512975
UPC 12 Digit	7818105129755

### Dimensions

Dimension - D inch	4.50 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Height inch	4.05 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	15.5 in
Dimension - N inch	1.12 in
Dimension - Outside Diameter inch	1.19 in
Dimension - Pad Width inch	3.25 in

### Electrical Ratings

Voltage - Maximum	230 kV
-------------------	--------

### Conductor Related

Conductor - ACCC Str Size	LINNET 431 Kcmil, ORIOLE 438 Kcmil, COPENHAGEN 230mm <sup>2</sup> , REYKJAVIK 235mm <sup>2</sup>
Conductor - Material	Aluminum

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)