

EQC632C

by Burndy
Catalog ID: EQC632C

Prop 65 Notice

Copper transformer ground connector. Fits all standard EEI-NEMA distribution transformers as tank grounding terminal.

Features: Fits All Standard EEI NEMA Distribution Transformers As A Tank Grounding Terminal, Stud Size: 1/2-13



Product Details

General

Application	For Used To Fit All Standard EEI-NEMA Distribution Transformers As A Tank Grounding Terminal
Installation Torque Recommended in-lb	275 LBS/in
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Screw Type	Hexagonal Bolt
Plating Type	Tin - Bright
Sub Brand	MECHANICAL CONNECTOR
Type	EQC632C
UPC	781810256350
UPC 12 Digit	7818102563500

Dimensions

Dimension - Bolt Size fraction	1/2
Dimension - Height inch	1.51 in
Dimension - L Length Overall mm	29 mm
Dimension - Length Overall inch	1.13 in
Dimension - Stud Size inch	21/32
Dimension - Threads per inch	13
Dimension - Width inch	0.38 in
Dimension - Width mm	10 mm

Conductor Related

Conductor - Copper Solid Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Solid Size Range	8 AWG-2 AWG
Conductor - Copper Str Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Size Range	8 AWG-2 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	RUS
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)