

BYNA32RTHT

by Burndy
Catalog ID: BYNA32RTHT

BURNDY; HYLUG; BYNA-RTHT, EHV; Features: Straight Compression terminal for 250 DegC ACSS transmission lines at 345 kV and over; For ACSS Conductor; RoHS Under Investigation.



Product Details

General

Connector Type	Terminal
Feature - Barrel Style	Tapered
Feature - Barrel Type	Long
Material	Aluminum
Physical Attribute - Number of Holes	4
UPC	621945433694
UPC 12 Digit	6219454336944

Dimensions

Dimension - Bolt Size fraction	1/2
Dimension - D inch	4.5 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	16.56 in
Dimension - N inch	1.12 in
Dimension - Outside Diameter inch	1.19 in
Dimension - Pad Width inch	3.25 in
Dimension - Thread Size	1/2
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - ACSS Str Size	336.4 (26/7) kcmil;336.4 (30/7) kcmil
Conductor - ACSS Str Size Range	336.4 (26/7) kcmil-336.4 (30/7) kcmil

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Logistics

Minimum Pack Quantity	0
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)