

BYNA36RT15HHT

by Burndy
Catalog ID: BYNA36RT15HHT

Prop 65 Notice

BURNDY; HYLUG; BYNA-RT-HHT, EHV; Features: Terminal and hardware; Full tension compression deadend for 250 Deg C rated ACSS transmission lines at 345 kV and over; 15 Deg NEMA Tap Pad Terminal; For ACSS Conductor; RoHS Compatible; Conductor Range (Main/Primary): 477 KCMIL ACSS.



Product Details

General

Connector Type	Terminal
Die Index	720
Feature - Barrel Style	Tapered
Feature - Barrel Type	Long
Material	Aluminum
Physical Attribute - Number of Holes	4
UPC	781810514184
UPC 12 Digit	7818105141844

Dimensions

Dimension - Bolt Size fraction	1/2
Dimension - D inch	4.5 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	16.76 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	1.41 in
Dimension - Pad Width inch	3.25 in
Dimension - Thread Size	1/2
Physical Attribute - Tongue Angle	15 Degree

Conductor Related

Conductor - ACSS Str Size	477 (20/7) kcmil;477 (22/7) kcmil;477 (24/7) kcmil;477 (26/7) kcmil;477 (30/7) kcmil
Conductor - ACSS Str Size Range	477 (20/7) kcmil-477 (30/7) kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)