



## CUSA442NTC

by Burndy  
Catalog ID: CUSA442NTC

Prop 65 Notice

Cu Alloy Hystack, 2 Holes, 10 AWG-750 kcmil, 600V-35kV, 1/2" stud, Tin Plated, Compression.

Features: HYSTACK is made from high conductivity copper and tin-plated to provide optimum corrosion resistance, Width: 1.12 IN, Length: 2.50 IN, Height: 1.5 IN

## Product Details

### General

Application	Designed to get terminals to the back end of a bus bar or other areas that require terminals to be elevated off the mounting surface
Connector Type	Terminal
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	STACKING ADAPTERS
Temperature Rating	194
Trade Name	HYSTACK™
Type	Standard Barrel, Tin Plated
UPC	781810269176
UPC 12 Digit	7818102691766

### Dimensions

Dimension - Height inch	1.50 in
Dimension - L Length Overall mm	76 mm
Dimension - Length Overall inch	3.00 in
Dimension - Stud Size inch	1/2
Dimension - Width inch	1.13 in
Dimension - Width mm	29 mm
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Str Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil
Conductor - Copper Str Size Range	10 AWG-750 kcmil
Conductor - Material	Copper
Conductor Type	CU C Str-Size

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)