



FD65C6T14

by Burndy
Catalog ID: FD65C6T14

Prop 65 Notice

Cast Cu Alloy Substation Stud Connector, Bolted, Stud to Pad, 1" - 14
Stud, 230 kV, Silicon Bronze H/W, 1075 Amp

Product Details

General

Application	Substation
Connector Type	Stud Connector
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Type	Studs
UPC	781810003633
UPC 12 Digit	7818100036333

Dimensions

Dimension - B Length fraction	1-3/4 in
Dimension - B Length inch	1.75 in
Dimension - Bolt Size fraction	3/8
Dimension - D inch	3.00 in
Dimension - L Length Overall mm	145 mm
Dimension - Length Overall inch	5.72 in
Dimension - N inch	0.62 in
Dimension - Pad Width inch	3.00 in
Dimension - Pin Diameter fraction	1 in
Dimension - Pin Diameter inch	1.000 in
Dimension - Thread Size	3/8-14
Dimension - Threads per inch	14

Electrical Ratings

Amperage Rating	1075 A
Rating - KVA	230 kV

Conductor Related

Conductor - Connection Combination	Stud to Pad
------------------------------------	-------------

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	2
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)