



## EA282

by Burndy  
Catalog ID: EA282

Prop 65 Notice

Copper alloy VERSILUG™ terminal; 1/0 - 4/0 AWG Stranded; 3/8" stud; 2-hole pad; 1" spacing; UL 468A/B

## Product Details

### General

Connector Type	Terminal
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Temperature Rating	194
Trade Name	VERSILUG™
Type	Bolted Lugs & Terminals
UPC	781810244425
UPC 12 Digit	7818102444255

### Dimensions

Dimension - B Length fraction	1-11/25 in
Dimension - B Length inch	1.44 in
Dimension - Height fraction	1.75 in
Dimension - Height inch	1.75 in
Dimension - Hole Size inch	0.44 in
Dimension - Hole Size mm	11 mm
Dimension - L Length Overall mm	100 mm
Dimension - Length Overall inch	3.94 in
Dimension - N inch	0.41 in
Dimension - Pad Width inch	1.06 in

### Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

### Conductor Related

Conductor - Copper Str Size	1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Size Range	1/0 -4/0 AWG
Conductor Type	CU C Str-Size

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	7
-----------------------	---

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)