



FD66D12T0

by Burndy
Catalog ID: FD66D12T0

Prop 65 Notice

Copper Stud Connectors

Product Details

General

Application	Substation
Connector Type	Stud Connector
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Configuration	4x4 - 4 holes
Physical Attribute - Pad Orientation	In-line
Plated	N
Plating Type	Unplated
Type	Studs
UPC	781810112953
UPC 12 Digit	7818101129533

Dimensions

Dimension - D inch	4.00 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Pad Width inch	4.00 in
Dimension - Pin Diameter fraction	1-1/4 in
Dimension - Pin Diameter inch	1.250 in

Electrical Ratings

Rating - KVA	230 kV
--------------	--------

Conductor Related

Conductor - Connection Combination	Stud to Pad
------------------------------------	-------------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	4
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)