



FD67C8W

by Burndy
Catalog ID: FD67C8W

Prop 65 Notice

Copper Stud Connectors

Product Details

General

Application	Substation
Connector Type	Stud Connector
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Configuration	3x3 - 4 holes
Physical Attribute - Pad Orientation	In-line
Plated	Y
Plating Type	Tin - Hot Dipped
Type	Studs
UPC	621945456440
UPC 12 Digit	6219454564400

Dimensions

Dimension - B Length inch	2.18 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	3.00 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - L Length Overall mm	171 mm
Dimension - Length Overall inch	6.75 in
Dimension - N inch	0.5 in
Dimension - Pad Width inch	3.00 in
Dimension - Pin Diameter inch	1.500 in
Dimension - Thread Size	1/2-12
Dimension - Threads per inch	12

Electrical Ratings

Rating - KVA	230 kV
--------------	--------

Conductor Related

Conductor - Connection Combination	Stud to Pad
------------------------------------	-------------

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	EX

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)