



FD645D8T0

by Burndy
Catalog ID: FD645D8T0

Prop 65 Notice

Copper Stud Connectors

Product Details

General

Application	Substation
Connector Type	Stud Connector
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Type	Studs
UPC	781810496589
UPC 12 Digit	7818104965899

Dimensions

Dimension - B Length fraction	1-3/4 in
Dimension - B Length inch	1.75 in
Dimension - Bolt Size fraction	3/8
Dimension - L Length Overall mm	179 mm
Dimension - Length Overall inch	7.06 in
Dimension - Pin Diameter fraction	7/8 in
Dimension - Pin Diameter inch	.875
Dimension - Thread Size	3/8-0

Electrical Ratings

Rating - KVA	230 kV
--------------	--------

Conductor Related

Conductor - Connection Combination	Stud to Pad
------------------------------------	-------------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX

UL Listed	No
-----------	----

Logistics

Minimum Pack Quantity	12
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)