



FD67T12CG14

by Burndy
Catalog ID: FD67T12CG14

Stud Connector, 1-1/2 IN Stud to 4 Holes NEMA Pad, Material: Cast Copper Alloy

Product Details

General

| | |
|---------------------------------------|--------------------|
| Application | Substation |
| Connector Type | Stud Connector |
| Installation Torque Recommended in-lb | 360 lbs-in |
| Material | Copper Alloy, Cast |
| Material - Hardware | Silicon Bronze |
| Physical Attribute - Pad Orientation | In-line |
| Plated | Y |
| Plating Type | Tin Plated |
| Type | Studs |
| UPC | 621945144484 |
| UPC 12 Digit | 6219451444844 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - B Length inch | 2.68 in |
| Dimension - Length Overall inch | 6.56 in |
| Dimension - Pin Diameter inch | 1.50 in |
| Dimension - Threads per inch | 12 |
| Dimension - Width inch | 2.88 in |

Electrical Ratings

| | |
|--------------|--------|
| Rating - KVA | 230 kV |
|--------------|--------|

Conductor Related

| | |
|------------------------------------|-------------|
| Conductor - Connection Combination | Stud to Bar |
|------------------------------------|-------------|

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Standards - RoHS Compliance Status | UI |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)